

The pedal set has elastomers four different length and three different hardness, to offer a large range of brake stiffness and travel options.

ATTENTION!!!
Use the 25mm elastomers - hardness independent - only for moderate pedal force. Due to the length at high pedal force they has the tendency for stalling over.

SOFT ELASTOMER IDENTIFICATION MARK: WITHOUT DOT

MEDIUM ELASTOMER IDENTIFICATION MARK: ONE DOT

HARD ELASTOMER IDENTIFICATION MARK: TWO DOTS

The hardness and length of applied elastomers determine how electronic sensors register the maximum pedal effort and the maximum pedal travel. Softer and longer elastomers give long travel but low registered pedal effort, whilst harder and shorter ones give short travel and higher registered pedal effort.

Pedal elastomer layout combinations. Elastomer hardness need to be selected.

- VERSION #01#**: 10mm ELASTOMER, 15mm ELASTOMER, 25mm ELASTOMER, 20mm ELASTOMER, 20mm ELASTOMER, 10mm ELASTOMER
- VERSION #02#**: 10mm ELASTOMER, 15mm ELASTOMER, 25mm ELASTOMER, 20mm ELASTOMER, 10mm ELASTOMER
- VERSION #03#**: 15mm ELASTOMER, 15mm ELASTOMER, 20mm ELASTOMER, 5mm SPACER WASHER, 20mm ELASTOMER, 15mm ELASTOMER, 10mm ELASTOMER
- VERSION #04#**: 15mm ELASTOMER, 15mm ELASTOMER, 20mm ELASTOMER, 5mm SPACER WASHER, 20mm ELASTOMER, 15mm ELASTOMER, 10mm ELASTOMER
- VERSION #05#**: 10mm ELASTOMER, 10mm ELASTOMER, 20mm ELASTOMER, 10mm SPACER WASHER, 5mm SPACER WASHER, 15mm ELASTOMER, 15mm ELASTOMER, 15mm ELASTOMER
- VERSION #06#**: 10mm ELASTOMER, 15mm ELASTOMER, 15mm ELASTOMER, 10mm SPACER WASHER, 5mm SPACER WASHER, 15mm ELASTOMER, 10mm ELASTOMER, 10mm ELASTOMER
- VERSION #07#**: 10mm ELASTOMER, 15mm ELASTOMER, 15mm ELASTOMER, 10mm SPACER WASHER, 5mm SPACER WASHER, 15mm ELASTOMER, 10mm ELASTOMER, 10mm ELASTOMER
- VERSION #08#**: 10mm ELASTOMER, 15mm ELASTOMER, 15mm ELASTOMER, 10mm SPACER WASHER, 5mm SPACER WASHER, 15mm ELASTOMER, 10mm ELASTOMER, 10mm ELASTOMER